



**CONSUTEC SA**  
Sistemi tecnici per l'edilizia


# Maximale Leinenlängen bei entsprechenden Raummassen in Metern

| Raumbreite (m) | Leinenzahl (Stk.) | Raumlänge       |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
|----------------|-------------------|-----------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
|                |                   |                 |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
|                |                   | von             | 1.76 | 2.01 | 2.26 | 2.51 | 2.76 | 3.01 | 3.26 | 3.51 | 3.76 | 4.01 | 4.26 | 4.51 | 4.76 | 5.01 | 5.26 | 5.51 | 5.76 |
|                |                   | bis             | 2.00 | 2.25 | 2.50 | 2.75 | 3.00 | 3.25 | 3.50 | 3.75 | 4.00 | 4.25 | 4.50 | 4.75 | 5.00 | 5.25 | 5.50 | 5.75 | 6.00 |
| 0.75           | 5                 | Leinenlänge (m) | 10   | 12   | 13   | 14   | 15   | 17   | 18   | 19   | 20   | 22   | 23   | 24   | 25   | 27   | 28   | 29   | 30   |
| 0.90           | 6                 | Leinenlänge (m) | 12   | 14   | 15   | 17   | 18   | 20   | 21   | 23   | 24   | 26   | 27   | 29   | 30   | 32   | 33   | 35   | 36   |
| 1.05           | 7                 | Leinenlänge (m) | 14   | 16   | 18   | 20   | 21   | 23   | 24   | 27   | 28   | 30   | 32   | 34   | 35   | 37   | 39   | 41   | 42   |
| 1.20           | 8                 | Leinenlänge (m) | 16   | 18   | 20   | 22   | 24   | 26   | 28   | 30   | 32   | 34   | 36   | 38   | 40   | 42   | 44   | 46   | 48   |
| 1.35           | 9                 | Leinenlänge (m) | 18   | 21   | 23   | 25   | 27   | 30   | 32   | 34   | 36   | 39   | 41   | 43   | 45   | 48   | 50   | 52   | 54   |
| 1.50           | 10                | Leinenlänge (m) | 20   | 23   | 25   | 28   | 30   | 33   | 35   | 38   | 40   | 43   | 45   | 48   | 50   | 53   | 55   | 58   | 60   |
| 1.65           | 11                | Leinenlänge (m) | 22   | 25   | 28   | 31   | 33   | 36   | 39   | 42   | 44   | 47   | 50   | 53   | 55   | 58   | 61   | 64   | 66   |
| 1.80           | 12                | Leinenlänge (m) | 24   | 27   | 30   | 33   | 36   | 39   | 42   | 45   | 48   | 51   | 54   | 57   | 60   | 63   | 66   | 69   | 72   |
| 1.95           | 13                | Leinenlänge (m) | 26   | 30   | 33   | 36   | 39   | 43   | 46   | 49   | 52   | 56   | 59   | 62   | 65   | 69   | 72   | 75   | 78   |
| 2.10           | 14                | Leinenlänge (m) | 28   | 32   | 35   | 39   | 42   | 46   | 49   | 53   | 56   | 60   | 63   | 67   | 70   | 74   | 77   | 81   | 84   |
| 2.25           | 15                | Leinenlänge (m) | 30   | 34   | 38   | 42   | 45   | 49   | 53   | 57   | 60   | 64   | 68   | 72   | 75   | 79   | 83   | 87   | 90   |
| 2.40           | 16                | Leinenlänge (m) | 32   | 36   | 40   | 44   | 48   | 52   | 56   | 60   | 64   | 68   | 72   | 76   | 80   | 84   | 88   | 92   | 96   |
| 2.55           | 17                | Leinenlänge (m) | 34   | 39   | 43   | 47   | 51   | 56   | 60   | 64   | 68   | 73   | 77   | 81   | 85   | 90   | 94   | 98   | 102  |
| 2.70           | 18                | Leinenlänge (m) | 36   | 41   | 45   | 50   | 54   | 59   | 63   | 68   | 72   | 77   | 81   | 86   | 90   | 95   | 99   | 104  | 108  |
| 2.85           | 19                | Leinenlänge (m) | 38   | 43   | 48   | 53   | 57   | 62   | 67   | 72   | 76   | 81   | 86   | 91   | 95   | 100  | 105  | 110  | 114  |
| 3.00           | 20                | Leinenlänge (m) | 40   | 45   | 50   | 55   | 60   | 65   | 70   | 75   | 80   | 85   | 90   | 95   | 100  | 105  | 110  | 115  | 120  |
| 3.15           | 21                | Leinenlänge (m) | 42   | 48   | 53   | 58   | 63   | 69   | 74   | 79   | 84   | 90   | 95   | 100  | 105  | 111  | 116  | 121  |      |
| 3.30           | 22                | Leinenlänge (m) | 44   | 50   | 55   | 61   | 66   | 72   | 77   | 83   | 88   | 94   | 99   | 105  | 110  | 116  | 121  |      |      |
| 3.45           | 23                | Leinenlänge (m) | 46   | 52   | 58   | 64   | 69   | 75   | 81   | 87   | 92   | 98   | 104  | 110  | 115  | 121  |      |      |      |
| 3.60           | 24                | Leinenlänge (m) | 48   | 54   | 60   | 66   | 72   | 78   | 84   | 90   | 96   | 102  | 108  | 114  | 120  |      |      |      |      |


## Artikelnummern zu Normtypen

| Norm                 | 30       | 40       | 60       | 80       | 100       |
|----------------------|----------|----------|----------|----------|-----------|
| Artikelnummer        | T3.044   | T3.046   | T3.048   | T3.050   | T3.052    |
| Leinenlänge (+/- 5%) | 30 Meter | 40 Meter | 60 Meter | 80 Meter | 100 Meter |
| Anzahl Leinen        | 10       | 13       | 17       | 20       | 22        |

Tipo A



Tipo B



Tipo C

